



AN EXCHANGE OF TECHNICAL INFORMATION

**Number:** TL004 – 2024

**Subject:** ML5 Configuration CF6

**Released:** March 19, 2024

When using software 6326 and higher for the ML5, model configuration card .cf6 (included within the release) is required. The .cf6 file allows for the recording of additional inputs within the controller by model number configuration.

When upgrading from 6325 and less to 6326 and higher you will need to have both configuration files (.cf5 and .cf6) on the USB at the time of the upgrade. After completing the upgrade, only the .cf6 file is required.

To load both versions onto the drive: drag and drop the .cf5 file onto the USB stick loaded with 6326 and higher. Version 6326+ will already have a .cf6 file. Note, it is recommended that you confirm that you have the latest .cf6 release as new model numbers are continually being added in between software releases.

To check the release revision, once powered up select Cd20 (Config/Model Number) and press enter. By pressing enter, the configuration file number will be displayed (i.e., CF231115).



Note: DataLINE software will only support up to 16 inputs. Above 16 will require the use of ContainerLINK.

Service Engineering / Container Products

*Please circulate copies of this bulletin to all service and management personnel as soon as possible.*